

**Garant****Compact clamp, Reach A: 67mm****Order data**

Order number	370143 67
GTIN	4062406233143
Item class	31K

**Description****Advantage:**

- **Compact design, dirt-repellent and chip-repellent.**
- **Height scale permits quick pre-setting of the clamping height.**
- **Captive pressure piece. Pressure piece adapters are attached by a magnetic insert.**
- **Easy assembly using the clamping arm.**

**Material:**

Body and pressure arm of heat treatable steel.

**Supplied with:**

Compact clamp, T-nut for width 14 mm and screw M12.

**Optional extras:**

Pressure piece set No. 370148.

**Technical description**

maximum torque	105 Nm
Reach A	67 mm
maximum clamping force	12 kN

Length L	95 mm
Width B	40 mm
Height H	81 mm
Clamping height S	0 - 100 mm
for thread M	M12
Type of product	Compact clamp

---

## Accessories

Pressure piece set, 3 pieces Type 3	370148 3
Riser block for compact clamps Height H 80 mm	370146 80