

FLEX**Polishing machine, Type: PE14-118****Order data**

| | |
|--------------|-----------------|
| Order number | 077771 PE14-118 |
| GTIN | 4030293166806 |
| Item class | 03S |

Description**Version:**

- **Microprocessor electronics with stepless speed pre-set, constant speed control by tachogenerator, overload protection, restart inhibit after a power failure and temperature monitoring.**
- **Powerful 1400 Watt motor with high-performance fan for optimum cooling.**
- **Flat gear head reduces the distance to the surface. This allows the machine to be securely guided in any position.**
- **Grip handle: ergonomically shaped with SoftGrip.**
- **Accelerator switch for slow and responsive starting (starting speed at step 1 (250/min)) and stopping in continuous operation.**
- **Optimised air circulation for the best possible cooling of the motor and gear. No irritating exhaust air for the user.**
- **With rubberised resting bar for safe setting down**

Application:

Specially for working on large horizontal and vertical surfaces. For the automotive, maritime and aviation sectors. Polishes at extremely low rotational speed and high torque, e.g. for heat-sensitive surfaces.

Technical description

| | |
|----------------------------|-------------|
| Manufacturer's designation | PE 14-1 180 |
|----------------------------|-------------|

| | |
|--------------------------|------------------------------|
| Weight | 2.3 kg |
| Power consumption | 1400 W |
| Speed range | 250 - 1380 min ⁻¹ |
| Width | 117 mm |
| Cable length | 4 m |
| Toolholder | M 14 |
| Length | 405 mm |
| maximum polishing tool Ø | 250 mm |
| Power supply | Mains operated |
| Type of product | Polishing machine |