

Garant**Cordless LED floodlight, Type: 3000****Order data**

Order number	081445 3000
GTIN	4062406232894
Item class	01A

Description**Version:**

Cordless LED battery floodlight with sturdy aluminium casing for everyday use in rough environments.

- **High-performance COB LED modules.**
- **Dimmable in 5 steps from 10 to 100 %.**
- **Practical monitoring of the state of charge of the battery by LED display directly on the lamp.**
- **Base with integral 10 mm hole, for mounting on suitable stands.**

Flexibility in use. Cordless or mains power.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Including battery charger.

Technical description

Type of rechargeable battery	Lithium-ion
------------------------------	-------------

Power supply	Rechargeable battery-powered
Weight	1720 g
Battery capacity	4.4 Ah
Overall length	234 mm
Illumination time	1 - 14 h
Overall height	233 mm
Illumination	400 - 4000 lm
Number of rechargeable batteries contained	1
Bulb	LED module
IP Index of Protection	IP 67
Overall width	88 mm
Battery voltage	11.1 V
ATEX zone	no
Type of product	Floodlight

Accessories

Cordless lamp spare parts Type 7	081434 7
Cordless lamp spare parts Type 5	081434 5
Battery charger Type CHARGER	081456 CHARGER
Li-ion battery Battery capacity 4400 mAh	081431 4400
Spare lens with seal Type 2	081454 2
Cordless lamp spare parts Type 6	081434 6