

**Copper pipe bending pliers, for pipe outer Ø: 15mm****Order data**

Order number	821310 15
GTIN	4062406237578
Item class	82A

Description**Version:**

For bending angles up to 180° with smallest possible radius and no deformation of the pipe.
Forming segment with graduations.

Lightweight design for non-fatiguing work. Non-slip handle.

Application:

For bending soft copper pipes. Reverse curves can be bent in all directions, without transitions or shoulders, because the pliers can also be set in the middle of the pipe.

Technical description

Bending radius (centre of pipe)	54 mm
for pipe outer Ø	15 mm
maximum bending angle	180 degrees
Type of product	Bending machine