

**Copper pipe bending pliers, for pipe outer Ø: 16mm****Order data**

Order number	821310 16
GTIN	4062406237585
Item class	82A

**Description****Version:**

For bending angles up to 180° with smallest possible radius and no deformation of the pipe.  
Forming segment with graduations.

Lightweight design for non-fatiguing work. Non-slip handle.

**Application:**

For bending soft copper pipes. Reverse curves can be bent in all directions, without transitions or shoulders, because the pliers can also be set in the middle of the pipe.

**Technical description**

for pipe outer Ø	16 mm
Bending radius (centre of pipe)	58 mm
maximum bending angle	180 degrees
Type of product	Bending machine