



External micrometer, Measuring range: 0-25mm



Order data

Order number	420430 0-25
GTIN	4062406237509
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	0 - 25 mm
Calibration	B1
Scale divisions	0.01 mm
Barrel Ø	20.5 mm
Spindle Ø	6.5 mm
Micrometer barrel graduations	1/50 mm
Standard	DIN 863
Ratchet	yes
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer without setting dimension maximum measuring range 100 mm	022010 100
Calibration External micrometer without setting dimension maximum measuring range 25 mm	022000 25