



External micrometer, Measuring range: 25-50mm



Order data

Order number	420430 25-50
GTIN	4062406237714
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Scale divisions	0.01 mm
Micrometer barrel graduations	1/50 mm
Calibration	B2
Measuring range	25 - 50 mm
Barrel Ø	20.5 mm
Spindle Ø	6.5 mm
Standard	DIN 863
Ratchet	yes
Measurement technology	analogue

Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Micrometer setting standard overall length 25 mm	421100 25
--	-----------