



External micrometer, Measuring range: 50-75mm



Order data

Order number	420430 50-75
GTIN	4062406237721
Item class	42B

Description

Version:

Precision lapped, carbide-tipped measuring faces.

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Micrometer barrel graduations	1/50 mm
Calibration	B2
Barrel Ø	20.5 mm
Scale divisions	0.01 mm
Spindle Ø	6.5 mm
Measuring range	50 - 75 mm
Standard	DIN 863
Ratchet	yes

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100
DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100

Accessories

Micrometer setting standard overall length 50 mm	421100 50
--	-----------