

**External micrometer, Measuring range: 75-100mm****Order data**

Order number	420430 75-100
GTIN	4062406237738
Item class	42B

Description**Version:****Precision lapped, carbide-tipped measuring faces.**

Hardened and ground measuring spindle. Locking by clamping lever.

With ratchet and hand temperature protection. Barrel non-reflecting chrome-plated.

With clearly engraved, black divisions and numerals.

With combined sensitive ratchet for one-hand operation and operation within the bracket.

Supplied with:

From size 25-50 including 1 setting standard.

Technical description

Measuring range	75 - 100 mm
Calibration	B2
Micrometer barrel graduations	1/50 mm
Scale divisions	0.01 mm
Barrel Ø	20.5 mm
Spindle Ø	6.5 mm
Standard	DIN 863
Ratchet	yes

Measurement technology	analogue
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 100 mm	022050 100
Calibration External micrometer including setting dimension maximum measuring range 100 mm	022040 100

Accessories

Micrometer setting standard overall length 75 mm	421100 75
--	-----------