

**Garant**

**Water pump pliers with stepped fine adjustment, black, overall length: 180mm**



## Order data

Order number	706001 180
GTIN	4062406238971
Item class	71B

## Description

### Version:

Box joint designed to prevent fingers being trapped. Push-button **fine step adjustment**, which also allows for quick adjustments directly on the workpiece. Concave profile serrated jaws, self-clamping. The teeth also run against each other in the rear of the jaw for a tight grip. Surface manganese phosphated, polished teeth. Ergonomically shaped handles with non-slip plastic coating.

### Standard:

**DIN ISO 8976**

### Material:

Chrome vanadium steel, drop forged.

## Technical description

Jaw capacity for pipes	1.1/2 in
overall length	180 mm
Hexagon across flats	36 mm
Number of fine adjustment steps	19
Surface	manganese phosphated, polished jaws
Standard	DIN ISO 8976
Type of jaws	concave profile serrated jaws

Material	Chromium vanadium steel
non-sparking	no
Quick adjustment	yes
Stepped fine adjustment	yes
Self-locking	yes
Protection against trapping fingers	yes
Type of product	Pipe wrench and water pump pliers