

Garant**Electronics side cutter slim design, kW, overall length: 130mm****Order data**

Order number	726682 130
GTIN	4062406239220
Item class	71B

Description**Version:**

Professional diagonal side cutter with slightly shearing cut. Both cutter parts are very accurately put together using carefully machined holes and polished surfaces to ensure a precise cut. With opening spring and ergonomically designed handles for secure and comfortable use. **2-component grips** of dissipative material. **Suitable for ESD work.**

Material:

Made of carbon steel (C70), precision stamped and heat-treated, non-reflective phosphate.

Technical description

Cutting capacity copper wire up to Ø	0.8 mm
overall length	130 mm
Cutter length	8 mm
Head width	9.5 mm
electrostatic characteristic	EGB/ESD
Cutting chamfer	without bevel
Material	Carbon steel (C70)
Surface	phosphated, non-reflecting
Product name attribute	kW
with return spring	yes

Type of product

Cutting pliers