



Vernier caliper with extra long jaws, Measuring range: 800mm



Order data

Order number	415188 800
GTIN	4062406239503
Item class	41Z

Description

Version:

Vernier satin chrome-plated, anti-glare. Measuring faces hardened and ground. **Long jaws for measuring large components and component \varnothing .** With fine adjustment. Offset and rounded jaw ends for internal measurements.

With **extra long jaws**, without fine adjustment.

Technical description

Jaw length	300 mm
Standard	Manufacturer's standard
Calibration	A1
Packaging	sturdy box
Internal jaw \varnothing	20 mm
Error limit	0.17 mm
Weight	3.5 kg
Scale divisions	0.05 mm
Graduation	1/20 mm

Measuring range	0 - 800 mm
Measurement technology	analogue
Material	Stainless steel, INOX
all parts	hardened
Type of product	Workshop calipers

Services

DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000
CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000