

Garant**Abrasive flap disc long life ZA, flat, Ø 125 mm, Grit: 40****Order data**

| | |
|--------------|---------------|
| Order number | 565270 40 |
| GTIN | 4062406239947 |
| Item class | 51M |

Description**Version:**

- **Premium zirconium aluminium oxide (ZA) for maximum abrasive performance.**
- **Sturdy polyester cotton mixed fabric for ideal wear characteristics and stability, even when used on edges.**
- **Sturdy glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on low-power and high-power angle grinders.**

long life - very closely spaced flap strips, for **maximum tool life**.

Application:

General purpose abrasive disc operations, surface abrasion, material removal and edge smoothing.

Technical description

| | |
|-------------------|--------|
| Shape description | flat |
| Grit | 40 |
| Disc Ø | 125 mm |

| | |
|-----------------------------------------|-------------------------|
| Bore Ø | 22.23 mm |
| Grinding media | Zirconium abrasive (ZA) |
| Grinding medium code | ZA |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Product name attribute | Ø 125 mm |
| optimised for material | Steel |
| optimised for material | INOX |
| maximum circumferential speed | 80 m/s |
| Type of product | Abrasive flap disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|-------------------------------------------|----------------|----------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| Uni | suitable | | |
| dry | suitable | | |