

Garant**Eco toolholder, Form B8 radial left-hand, long, Shank Ø d1: 30mm**

Order data

Order number	319093 30
GTIN	4062406240745
Item class	31V

Description

Version:

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

Application:

Mainly for external machining.

Standard:

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

Technical description

b ₂	65 mm
Shank Ø D ₁	30 mm
l ₁	22 mm
Colour code for VDI shanks	VDI 30
h ₆	35 mm

Data sheet

h_1	20 mm
b_1	100 mm
l_2	40 mm
h_5	38 mm
h_2	29 mm
Shape	B
Type of product	VDI tool arbor