

**Garant****Eco toolholder, Form B7 radial right-hand, long, Shank Ø d1: 30mm**

## Order data

|              |               |
|--------------|---------------|
| Order number | 319091 30     |
| GTIN         | 4062406240721 |
| Item class   | 31V           |

## Description

**Version:**

- Case-hardened HRC 58 ±2.
- All functional faces ground.
- With ball type coolant nozzles.

**Application:**

Mainly for external machining.

**Standard:**

ISO 10889 / DIN 69880 / VDI 3425, sheet 2.

## Technical description

|                        |        |
|------------------------|--------|
| Shank Ø D <sub>1</sub> | 30 mm  |
| l <sub>1</sub>         | 22 mm  |
| l <sub>2</sub>         | 40 mm  |
| b <sub>1</sub>         | 100 mm |
| h <sub>6</sub>         | 35 mm  |

## Data sheet

|                            |                |
|----------------------------|----------------|
| $h_1$                      | 20 mm          |
| Colour code for VDI shanks | VDI 30         |
| $h_2$                      | 29 mm          |
| $h_5$                      | 38 mm          |
| $b_2$                      | 65 mm          |
| Shape                      | B              |
| Type of product            | VDI tool arbor |