



VDI parting-off toolholder blade height 32, Shank \varnothing d1: 40-UEKmm



Order data

Order number	319149 40-UEK
GTIN	2050002040069
Item class	33E

Description

Version:

For use on DMG Gildemeister CTX CNC lathes with radial turrets.

- **With double serrations on the VDI shank for left-handed and right-handed use.**
- **With ball spray nozzle for optimum cooling of the cutting edge.**
- **Clamping the grooving tool by means of a clamping strip.**
- **Height adjustment range ± 1 mm.**

Application:

Allows parting-off tools of different makes to be used.

Suitable for:

DMG Gildemeister CTX.

Note:

Sizes 30-UEK and 40-UEK as overhead versions.

Technical description

Colour code for VDI shanks	VDI 40
Height H	100 mm
L ₁	88.5 mm
Width B ₁	35 mm

Width B ₂	60 mm
Width B ₃	48 mm
Type of product	VDI parting-off toolholder