

**Locking C clamp with movable jaws, overall length: 275mm****Order data**

Order number	709101 275
GTIN	4062406241025
Item class	72B

Description**Version:**

Narrow jaws with high C shape; wide clearance. Sturdy spring steel body. Nickel-plated handles and clamping jaws.

With movable jaws to protect the component.

Application:

Particularly suitable for clamping profiled material with high flanges or bulky components.

Material:

Chrome vanadium steel clamping jaws, drop forged.

Spare part:

Spare springs No. 708301 sizes 5 and 10.

Technical description

overall length	275 mm
Jaw capacity	75 mm
Type of product	Grip wrench

Accessories

Spring Type 10	708301 10
----------------	-----------

