

**Sheet metal clamp, overall length: 180mm****Order data**

Order number	709701 180
GTIN	4062406241087
Item class	72B

Description**Version:**

Particularly wide and flat clamping jaws. Sturdy spring steel body. Fully nickel-plated.

Application:

Particularly suitable for holding, bending, and flanging sheet metal.

Material:

Chrome vanadium steel clamping jaws.

Spare part:

Spare spring No. 708301 size 7.

Technical description

overall length	180 mm
Jaw capacity	45 mm
Jaw width	80 mm
Type of product	Grip wrench

Accessories

Spring Type 10	708301 10
----------------	-----------