

Garant**Abrasive cloth (A) robust, highly flexible, 230×280 mm, Grit: 150****Order data**

| | |
|--------------|---------------|
| Order number | 556790 150 |
| GTIN | 4045197807786 |
| Item class | 51E |

Description**Version:**

Densely woven cotton fabric, evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Very good grain adhesion, high abrasive performance and long working life. **Sheet size 230×280 mm.**

Very **sturdy and highly flexible abrasive cloth** (resistant to oil and petroleum). Moulds itself ideally to the workpiece geometry. Can be torn in longitudinal direction to yield clean edges along the weave without fraying.

Application:

Universally applicable, primarily for rubbing down by hand (for rubber sanding block see No. 557600).

Technical description

| | |
|------------------------|-----------------|
| Grit | 150 |
| Grit designation | medium |
| Grinding media | Aluminium oxide |
| Grinding medium code | A |
| Sanding disc width | 280 mm |
| Sanding disc length | 230 mm |
| Product name attribute | 230×280 mm |

Type of product

Abrasive cloth

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |

Accessories

| | |
|----------------------|--------|
| Rubber sanding block | 557600 |
| Steel backing plate | 556950 |