

Garant

Economy roll of abrasive cloth (A) robust, highly flexible, 115 mm×50 m, Grit: 60

**Order data**

Order number	556980 60
GTIN	4045197808042
Item class	51E

Description**Version:**

Densely woven, robust and **highly flexible** cotton fabric (resistant to oil and petroleum) evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Moulds ideally to the workpiece geometry. **High abrasive performance and long tool life.**

Economy roll 115 mm wide for all popular orbital sanders. **Cloth is drawn from the middle of the roll**, ensures a tidy workplace. Allows the roll to be used right up to the last piece without damage.

Application:

Ideal for metal. Suitable also for wood and for abrading paint.

Technical description

Grit	60
Grit designation	coarse
Grinding media	Aluminium oxide
Grinding medium code	A

Economy roll width	115 mm
Economy roll length	50 m
Product name attribute	115 mm×50 m
integral tear-off cutter	yes
Type of product	Abrasive cloth

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		