

Garant**Interchangeable insert for magnetic gripper, PA, Ø / height: 80/40mm****Order data**

| | |
|--------------|---------------|
| Order number | 358716 80/40 |
| GTIN | 4062406241810 |
| Item class | 31V |

Description**Version:**

Exchangeable plates in polyamide PA6.

Application:

Introduction of the matching contour of the finished workpiece for close-fitting parting off (max. 50 rpm) and transport of the component. Connection to the magnetic gripper by 4 screws.

Note:

The exchangeable plates can also be made in-house. As well as the introduction of workpiece geometries for machining, additive printing processes can also be used.

Technical description

| | |
|-----------------------|------------------|
| Ø D ₁ | 80 mm |
| Ø D ₂ | 50 mm |
| Height H ₂ | 27 mm |
| Height H ₁ | 40 mm |
| Type of product | Magnetic gripper |

