

**Garant****Interchangeable insert for magnetic gripper, PA, Ø / height: 120/40mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 358716 120/40 |
| GTIN         | 4062406241834 |
| Item class   | 31V           |

**Description****Version:**

Exchangeable plates in polyamide PA6.

**Application:**

Introduction of the matching contour of the finished workpiece for close-fitting parting off (max. 50 rpm) and transport of the component. Connection to the magnetic gripper by 4 screws.

**Note:**

The exchangeable plates can also be made in-house. As well as the introduction of workpiece geometries for machining, additive printing processes can also be used.

**Technical description**

|                       |                  |
|-----------------------|------------------|
| Ø D <sub>1</sub>      | 120 mm           |
| Ø D <sub>2</sub>      | 90 mm            |
| Height H <sub>2</sub> | 27 mm            |
| Height H <sub>1</sub> | 40 mm            |
| Type of product       | Magnetic gripper |

