



Hydraulic chuck BASIC short, slim, HSK-A 63, Clamping range \varnothing D1: 8mm



Order data

| | |
|--------------|---------------|
| Order number | 307507 8 |
| GTIN | 4062406240097 |
| Item class | 32A |

Description

Version:

- Axial length adjustment, adjustment travel 10 mm.
- With RFID/Balluffchip bore.

Application:

- High metal removal rate (but not for extreme heavy machining).
- For drilling, reaming, and milling.

Optional extras:

Reducing sleeves No. 302135 – 302187, coolant tube No. 309880, socket wrench No. 309890, parallel wipers No. 343720.

Note:

A-dimension = 200 mm available on request!

Technical description

| | |
|---------------------------------------|-------|
| Adjustment travel V | 10 mm |
| Overhang dimension A | 70 mm |
| Thread M | M6 |
| L ₃ | 24 mm |
| \varnothing D ₂ | 28 mm |
| Clamping \varnothing D ₁ | 8 mm |

| | |
|---------------------------------------|--------------------------|
| External Ø D | 50 mm |
| Adapter | HSK-A 63 |
| Arbor standard | ISO 12164-1 |
| Arbor standard | DIN 69893 |
| Arbor standard | DIN 69882-7 |
| Shape | A |
| Through-coolant | yes, with max. 80 bar |
| Balance quality G at rotational speed | G 2.5 at 25,000 rpm |
| Concentricity | ≤ 3 µm |
| Machining strategy | HSC |
| Balluffchip bore | yes |
| Type of product | Hydraulic clamping chuck |

Accessories

| | |
|---|----------|
| Cylindrical cleaner Plastic Pin Ø 8 mm | 343720 8 |
|---|----------|