

Garant

Economy roll of abrasive cloth (A) robust, highly flexible, 25 mm × 50 m, Grit: 40



Order data

| | |
|--------------|---------------|
| Order number | 556960 40 |
| GTIN | 4045197808332 |
| Item class | 51E |

Description

Version:

Densely woven, robust and **highly flexible** cotton fabric (resistant to oil and petroleum) evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Moulds ideally to the workpiece geometry. **High abrasive performance and long tool life.**

Economy roll in a handy dispenser box with viewing slot for quick monitoring of the remaining cloth. With high-quality cut-off blade.

Application:

Ideal for metal. Suitable also for wood and for abrading paint.

Technical description

| | |
|------------------|------------------------------|
| Grit designation | coarse |
| Dispenser height | 312 mm |
| Dispenser depth | 312 mm |
| Grinding media | Standard aluminium oxide (A) |

| | |
|--------------------------|----------------|
| Grinding medium code | A |
| Economy roll width | 25 mm |
| Economy roll length | 50 m |
| Product name attribute | 25 mm × 50 m |
| integral tear-off cutter | yes |
| Type of product | Abrasive cloth |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable only under restricted conditions | | |
| INOX | suitable | | |
| Ti | suitable only under restricted conditions | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Paint | suitable only under restricted conditions | | |
| Uni | suitable | | |
| dry | suitable | | |