

**Garant**

**Economy roll of abrasive cloth (A) robust, highly flexible, 25 mm × 50 m, Grit: 120**

**Order data**

Order number	556960 120
GTIN	4045197808370
Item class	51E

**Description****Version:**

Densely woven, robust and **highly flexible** cotton fabric (resistant to oil and petroleum) evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Moulds ideally to the workpiece geometry. **High abrasive performance and long tool life.**

**Economy roll in a handy dispenser box** with viewing slot for quick monitoring of the remaining cloth. With high-quality cut-off blade.

**Application:**

**Ideal for metal.** Suitable also for wood and for abrading paint.

**Technical description**

Grit designation	medium
Dispenser height	312 mm
Dispenser depth	312 mm
Grinding media	Standard aluminium oxide (A)

Grinding medium code	A
Economy roll width	25 mm
Economy roll length	50 m
Product name attribute	25 mm × 50 m
integral tear-off cutter	yes
Type of product	Abrasive cloth

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		