

**Garant**

**Face mill arbor Form ADB with cooling channel bore, SK 40 A = 200, Spigot  $\varnothing$  d1: 27mm**


**Order data**

Order number	301075 27
GTIN	4062406242114
Item class	31A

**Description**
**Version:**

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.
- With 4 cooling channel bores.
- All shanks hard turned (for smooth running!).

**Supplied with:**

Lock screw.

**Optional extras:**

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

**Technical description**

Overhang dimension A	200 mm
Spare milling cutter lock screw No. 309860 / 309861	27
Spigot $\varnothing$ d <sub>1</sub>	27 mm
Suitable toggle spanner No. 309840	27
External $\varnothing$ D	50 mm

Milling mandrel length $L_4$	21 mm
Clamping $\varnothing D_1$	27 mm
Adapter	SK 40 A = 200
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	ADB
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor