

**Garant**

**Economy roll of abrasive cloth (A) robust, highly flexible, 25 mm × 50 m, Grit: 180**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 556960 180    |
| GTIN         | 4045197808394 |
| Item class   | 51E           |

**Description****Version:**

Densely woven, robust and **highly flexible** cotton fabric (resistant to oil and petroleum) evenly spread with synthetic resin bonded **standard aluminium oxide (A)**. Moulds ideally to the workpiece geometry. **High abrasive performance and long tool life.**

**Economy roll in a handy dispenser box** with viewing slot for quick monitoring of the remaining cloth. With high-quality cut-off blade.

**Application:**

**Ideal for metal.** Suitable also for wood and for abrading paint.

**Technical description**

|                  |                              |
|------------------|------------------------------|
| Grit designation | fine                         |
| Dispenser depth  | 312 mm                       |
| Dispenser height | 312 mm                       |
| Grinding media   | Standard aluminium oxide (A) |

|                          |                |
|--------------------------|----------------|
| Grinding medium code     | A              |
| Economy roll width       | 25 mm          |
| Economy roll length      | 50 m           |
| Product name attribute   | 25 mm × 50 m   |
| integral tear-off cutter | yes            |
| Type of product          | Abrasive cloth |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable only under restricted conditions |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Paint                          | suitable only under restricted conditions |                |          |
| Uni                            | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |