

**Fine crepe adhesive tape set, natural, Width×length (mm× m): 24X50****Order data**

Order number	083769 24X50
GTIN	4062406242244
Item class	02A

**Description****Version:**

General-purpose adhesive tapes for numerous areas of application such as repairs, protection, wrapping up and packaging.

Slightly creped tape with good adhesive strength for short-term masking of smooth substrates in indoor areas. Temperature-resistant up to 60°C.

**Recommendation:**

Before bonding, check that the substrate is suitable.

Adhesive: Natural rubber

Thickness: 0.14 mm

Number of adhesive tapes: 9

**Technical description**

temperature-resistant up to	60 °C
Colour	natural
Backing material	Flat crepe
Application	Binding

## Data sheet

Application	Masking
Application	Masking
Application	Securing
Tensile strength	3 N/mm
Adhesive	Natural rubber
"Best before" date	12 mo
Length	50 m
Stretch capability	10 %
Thickness	0.14 mm
Adhesive strength on steel	0.32 N/mm
Type of adhesive tape	single-sided
Storage humidity	50 %
Liner present	no
Width	24 mm
Storage temperature	20 °C
Number of adhesive tapes	9
Type of product	Adhesive tape