



Fine crepe adhesive tape set, natural, Width×length (mm× m): 18X50



Order data

Order number	083769 18X50
GTIN	4062406242268
Item class	02A

Description

Version:

General-purpose adhesive tapes for numerous areas of application such as repairs, protection, wrapping up and packaging.

Slightly creped tape with good adhesive strength for short-term masking of smooth substrates in indoor areas. Temperature-resistant up to 60°C.

Recommendation:

Before bonding, check that the substrate is suitable.

Adhesive: Natural rubber

Thickness: 0.14 mm

Number of adhesive tapes: 12

Technical description

"Best before" date	12 mo
temperature-resistant up to	60 °C
Tensile strength	3 N/mm
Type of adhesive tape	single-sided

Data sheet

Application	Binding
Application	Masking
Application	Masking
Application	Securing
Storage humidity	50 %
Storage temperature	20 °C
Thickness	0.14 mm
Adhesive strength on steel	0.32 N/mm
Liner present	no
Adhesive	Natural rubber
Colour	natural
Width	18 mm
Backing material	Flat crepe
Length	50 m
Number of adhesive tapes	12
Stretch capability	10 %
Type of product	Adhesive tape