



Precision adhesive tape set, Width×length (mm× m): 30X50



Order data

Order number	083772 30X50
GTIN	4062406242374
Item class	02A

Description

Version:

General-purpose adhesive tapes for numerous areas of application such as repairs, protection, wrapping up and packaging.

For sharp edges to paint finishes on both smooth and rough substrates; UV-resistant.

- **Thin standard masking tape made from special paper (washi) for sharp edges to paint on smooth and slightly rough substrates**
- **Good adhesion and good tear resistance**
- **Duration of use indoors up to 3 months and up to 4 weeks outdoors**

Recommendation:

Before bonding, check that the substrate is suitable.

Adhesive: Acrylate

Thickness: 0.08 mm

Number of adhesive tapes: 8

Technical description

Length	50 m
Number of adhesive tapes	8

Data sheet

Width	30 mm
Colour	orange
Adhesive strength on steel	0.11 N/mm
temperature-resistant up to	100 °C
Liner present	no
Storage humidity	50 %
Type of adhesive tape	single-sided
Storage temperature	20 °C
Stretch capability	4 %
Thickness	0.08 mm
"Best before" date	12 mo
Special features	UV-resistant
Special features	tearable by hand
Special features	sharp edge to the paint
Adhesive	Acrylate
Application	Binding
Application	Securing
Application	Masking
Application	Masking
Tensile strength	3.8 N/mm
Type of product	Adhesive tape