

**Precision adhesive tape set, Width×length (mm× m): 18X50****Order data**

Order number	083772 18X50
GTIN	4062406242336
Item class	02A

Description**Version:**

General-purpose adhesive tapes for numerous areas of application such as **repairing, protecting, masking and packaging.**

For sharp edges to paint finishes on both smooth and rough substrates; UV-resistant.

- **Thin standard masking tape made from special paper (washi) for sharp edges to paint on smooth and slightly rough substrates.**
- **Good tack and good tear resistance.**
- **Duration of use indoors up to 3 months and up to 4 weeks outdoors.**

Recommendation:

Before bonding, check that the substrate is suitable.

Technical description

Number of adhesive tapes	12
Thickness	0.08 mm
Length	50 m
Stretch capability	4 %

Storage humidity	50 %
Adhesive strength on steel	0.11 N/mm
Tensile strength	3.8 N/mm
Application	Binding
Application	Securing
Application	Masking
Application	Masking
Type of adhesive tape	single-sided
Adhesive	Acrylate
Special features	UV-resistant
Special features	tearable by hand
Special features	sharp edge to the paint
Storage temperature	20 °C
Colour	orange
Liner present	no
Width	18 mm
temperature-resistant up to	100 °C
"Best before" date	12 mo
Type of product	Adhesive tape