



## Side lock arbor Form AD, SK 40 short, Clamping range $\varnothing$ D1: 10mm



### Order data

Order number	300205 10
GTIN	4062406242206
Item class	32A

### Description

#### Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

#### Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

External $\varnothing$ D	35 mm
Clamping $\varnothing$ D <sub>1</sub>	10 mm
Overhang dimension A	50 mm
Spare clamping screw No. 30 9900	10
Adapter	SK 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 18,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

---

## Accessories

Spare clamping screw for chucks with clamping Ø D1 10 mm	309900 10
--	-----------