



Side lock arbor Form AD with cooling channel bores, SK 40 short, Clamping range \varnothing D1: 18mm



Order data

Order number	300225 18
GTIN	4062406242657
Item class	32A

Description

Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

With cooling channel bores. Cannot be plugged.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Spare clamping screw No. 30 9900	16
External \varnothing D	50 mm
Clamping \varnothing D ₁	18 mm
Overhang dimension A	63 mm
Adapter	SK 40 short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD

Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping Ø D1 16 mm	309900 16
--	-----------