



Side lock arbor Form AD, SK 50 short, Clamping range \varnothing D1: 25mm



Order data

Order number	300315 25
GTIN	4062406243043
Item class	32A

Description

Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

External \varnothing D	65 mm
Overhang dimension A	80 mm
Clamping \varnothing D ₁	25 mm
Spare clamping screw No. 30 9900	25
Adapter	SK 50 short
Standard	DIN 6359
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 15,000 rpm

Concentricity	≤ 3 μm
Machining strategy	HPC
Type of product	Side lock arbor

Accessories

Spare clamping screw for chucks with clamping Ø D1 25 mm	309900 25
--	-----------