



## Side lock arbor Form AD, SK 50 short, Clamping range $\varnothing D_1$ : 6mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 300315 6      |
| GTIN         | 4062406242961 |
| Item class   | 32A           |

### Description

#### Version:

With Balluff/RFID chip bore.

All shanks fine bead blasted. Balancing quality G 6.3 / 18,000 rpm.

#### Application:

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

### Technical description

|                                       |                     |
|---------------------------------------|---------------------|
| External $\varnothing D$              | 25 mm               |
| Clamping $\varnothing D_1$            | 6 mm                |
| Overhang dimension A                  | 63 mm               |
| Spare clamping screw No. 30 9900      | 6                   |
| Adapter                               | SK 50 short         |
| Standard                              | DIN 6359            |
| Arbor standard                        | ISO 7388-1          |
| Shape                                 | AD                  |
| Balance quality G at rotational speed | G 6.3 at 15,000 rpm |

|                    |                 |
|--------------------|-----------------|
| Concentricity      | ≤ 3 μm          |
| Machining strategy | HPC             |
| Type of product    | Side lock arbor |

---

## Accessories

|   |          |
|---|----------|
| Spare clamping screw for chucks with clamping Ø D1 6 mm | 309900 6 |
|---|----------|