

Garant**ER mini mono-nut for HiRunER mini collet chuck, for ER: 11M****Order data**

Order number	309618 11M
GTIN	4062406243487
Item class	31Z

Description**Version:**

Slim, symmetrical design.

Thread and taper ground in a single setup for highest concentricity.

Suitable for :

HiRunER mini collet chuck.

Precision ER collet chuck No. 300643; 302839; 302844; 305518; 305524.

Optional extras:

ER chuck key No. 309757; 309758.

Note:

Collet chuck and clamping nut are balanced separately!

Standard: DIN 6499 D

Overall length L: 19.1 mm

External Ø D: 16 mm

Thread: M20×1

maximum tightening torque: 20 N·m

Technical description

Overall length L	19.1 mm
Thread	M20×1

External Ø D	16 mm
maximum tightening torque	20 N·m
Standard	DIN 6499 D
Type of product	Clamping nut

Accessories

HiRunER roller bearing wrench for torque wrench Type 11M	309758 11M
HiRunER roller bearing wrench Type 11M	309757 11M