

**Garant****ER mini mono-nut for HiRunER mini collet chuck, for ER: 16M****Order data**

Order number	309618 16M
GTIN	4062406243494
Item class	31Z

**Description****Version:**

Slim, symmetrical design.

Thread and taper ground in a single setup for highest concentricity.

**Suitable for :**

HiRunER mini collet chuck.

Precision ER collet chuck No. 300643; 302839; 302844; 305518; 305524.

**Optional extras:**

ER chuck key No. 309757; 309758.

**Note:**

Collet chuck and clamping nut are balanced separately!

Standard: DIN 6499 D

Overall length L: 21.6 mm

External Ø D: 24 mm

Thread: M24×0.75

maximum tightening torque: 30 N·m

**Technical description**

External Ø D	24 mm
for ER	16 mm

Overall length L	21.6 mm
Thread	M24×0.75
maximum tightening torque	30 N·m
Standard	DIN 6499 D
Type of product	Clamping nut

---

## Accessories

Single open ended spanner Width across flats 25 mm	613300 25
HiRunER roller bearing wrench Type 16M	309757 16M
HiRunER roller bearing wrench for torque wrench Type 16M	309758 16M