

Garant
Grooving toolholder 45°, left-hand, Shank / groove width w: 25/2

Order data

Order number	273763 25/2
GTIN	4062406243913
Item class	21W

Description
Application:

For free turning operations directly up to a shoulder, to create free undercuts for threading and grinding work.

Note:

- $\varnothing D_{\min} = 30 \text{ mm}$ (at $w = 3$).
- $\varnothing D_{\min} = 35 \text{ mm}$ (at $w = 2$).
- **Use only with a full radius groove turning insert No. 273735 – 273739.**
- **No standardised undercut according to DIN 509.**

Technical description

Groove width w	2 mm
Head length L_1	33 mm
Screw	279815 6 (TX25; 6 Nm)
Shank size	25 mm
Overall length L	150 mm
Functional width L_4	28 mm
min. groove width y	0.35 mm
t_{\min}	0.5 mm
Application type	left-hand
Through-coolant	no

axial grooving possible	no
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Clamping screw Type 5	279815 5
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600