

Garant**ER hydraulic collet with clamping nut ER25, Ød: 12mm****Order data**

Order number	319742 12
GTIN	4062406244750
Item class	31W

Description**Version:**

High flexibility for use with turning in static collet holders, but also when using driven tools. Best run-out characteristics.

For driven tools with external threads.

Advantage:

- **Ideal damping characteristics, resulting in optimum component surfaces and increased tool life.**
- **Quick and easy handling.**
- **Flexible use of reducing adapters.**
- **Perfect centring.**

Application:

Suitable for drilling, reaming, countersinking and also for use of boring bars.

Technical description

Thread M	M32×1.5
Ø d	12 mm
Ø d ₂	42 mm
Length L	51 mm

Type of product

Collet