



LED headlamp with rechargeable battery, Type: 300



Order data

Order number	081493 300
GTIN	4062406242480
Item class	02A

Description

Version:

LED work headlamp with wide spread of light for optimum illumination of the entire work area. Non-contact switching on and off, thanks to sensor system with 2 lighting levels.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

Charging cable.

Technical description

Type of rechargeable battery	Lithium-ion
Overall width	47 mm
Overall length	78 mm
Power supply	Rechargeable battery-powered
Illumination time	2 - 6 h
IP Index of Protection	IP 65
Illumination	100 - 300 lm
Weight	111 g
ATEX zone	no

Data sheet

Number of rechargeable batteries contained	1
Type of product	Headlamp