

BENNING**Multimeter, Manufacturer's designation: MMP3****Order data**

Order number	473300 MMP3
GTIN	4014650440846
Item class	47A

Description**Version:**

Sturdy plastic casing with large-format, 3½ inch, 4 inch or 4¾ inch LCD display.

Application:

Digital service multimeters for a wide range of applications. These provide a high level of safety and other additional functions. Digital multimeter, pocket-sized. Small and narrow (132×86×19 mm) - only 130 g in weight.

Standard:

IEC / DIN EN 061010-1 (DIN VDE 0411-1).

Supplied with:

Batteries, probe leads, compact protective case, operating instructions.

Technical description

Frequency	1 mHz – 5 MHz
Measurement process	RMS
AC voltage	0.1 mV – 600 V
Resistance	0.1 Ω – 40 MΩ

Basic accuracy	0.6 %
DC voltage	0.1 mV – 600 V
Number of batteries contained	2
Memory function	HOLD
Information displayed	5000
Article no of the battery / rechargeable battery fitted	081560 LR44
Overvoltage category	CAT III 300 V
Overvoltage category	CAT II 600 V
Calibration	I3
Capacitance	10 pF – 100 µF
Power supply	Battery-powered
Material of the housing	Plastic
Type of product	Multimeter

Services

CalibrationDigital multimeter Number of decimal places 3	027000 3
DAkkS calibrationDigital multimeter Number of decimal places 3	027010 3

Accessories

Button cell / special battery Battery type LR44	081560 LR44
---	-------------