

Garant**Set of parallels, underside magnetic, narrow, Length: 125mm**

Order data

Order number	366320 125
GTIN	4062406250478
Item class	31Z

Description

Version:**Accuracy:** Height tolerance ± 0.01 mm; width tolerance ± 0.02 mm.**Hardness:** 50-55 HRC.**Advantage:**

- **Flexible use thanks to integral rod magnet on the underside.**
- **Reduction in set-up time.**

Technical description

Width	5 mm
Number of strips	5 pair
Height	20 mm
Height	30 mm
Height	35 mm
Height	37 mm

Height	39 mm
Type of product	Pairs of parallels

Accessories

Pair of parallels, 125×5Magnetic underside Height 39 mm	366323 39
Pair of parallels, 125×5Magnetic underside Height 30 mm	366323 30
Pair of parallels, 125×5Magnetic underside Height 20 mm	366323 20
Pair of parallels, 125×5Magnetic underside Height 37 mm	366323 37
Pair of parallels, 125×5Magnetic underside Height 35 mm	366323 35