



Face mill arbor Form A, SK 40 A = 100, Spigot Ø d1: 22mm



Order data

Order number	301027 22
GTIN	4062406251925
Item class	32A

Description

Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.

All shanks fine bead blasted.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Technical description

Overhang dimension A	100 mm
Suitable toggle spanner No. 309840	22
Spigot Ø d ₁	22 mm
External Ø D	48 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Milling mandrel length L ₄	19 mm

Clamping $\varnothing D_1$	22 mm
Adapter	SK 40 A = 100
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor