



Face mill arbor Form A, SK 50 short, Spigot \varnothing d1: 32mm



Order data

Order number	301097 32
GTIN	4062406251970
Item class	32A

Description

Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.

All shanks fine bead blasted.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

Technical description

Spigot \varnothing d ₁	32 mm
Milling mandrel length L ₄	24 mm
External \varnothing D	78 mm
Suitable toggle spanner No. 309840	32
Spare milling cutter lock screw No. 309860 / 309861	32
Overhang dimension A	50 mm

Clamping $\varnothing D_1$	32 mm
Adapter	SK 50 short
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor