



## Face mill arbor Form A, SK 50 short, Spigot $\varnothing$ d1: 22mm



### Order data

Order number	301097 22
GTIN	4062406251956
Item class	32A

### Description

#### Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- Short series.
- Increased collar contact surface.
- With RFID/Balluffchip bore.

All shanks fine bead blasted.

#### Supplied with:

Lock screw.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

### Technical description

Spigot $\varnothing$ d <sub>1</sub>	22 mm
External $\varnothing$ D	48 mm
Spare milling cutter lock screw No. 309860 / 309861	22
Milling mandrel length L <sub>4</sub>	19 mm
Suitable toggle spanner No. 309840	22
Overhang dimension A	35 mm

Clamping $\varnothing D_1$	22 mm
Adapter	SK 50 short
Standard	DIN 6357
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 18,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor