



MT reducing adapter with tang, Form AD, SK 50 short, MT internal: 4



Order data

Order number	301185 4
GTIN	4062406252229
Item class	32A

Description

Version:

All shanks fine bead blasted.

- **Ground internally and externally.**
- **With Balluff/RFID chip bore.**

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Technical description

Overhang dimension A	95 mm
Morse taper internal	4
External Ø D	48 mm
Adapter	SK 50 short
Arbor standard	ISO 7388-1
Shape	AD
Balance quality G at rotational speed	G 6.3 at 12,000 rpm
Concentricity	≤ 8 µm
Type of product	Arbor adapter

