



## MT reducing adapter Form A, SK 40 short, MT internal: 3



### Order data

Order number	301245 3
GTIN	4062406252250
Item class	32A

### Description

#### Version:

- **Ground internally and externally.**
- **With Balluff/RFID chip bore.**

All shanks fine bead blasted.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

### Technical description

External Ø D	40 mm
Morse taper internal	3
Overhang dimension A	70 mm
Adapter	SK 40 short
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 8 µm
Type of product	Arbor adapter

