



MT reducing adapter Form A, SK 50 short, MT internal: 4



Order data

Order number	301255 4
GTIN	4062406252298
Item class	32A

Description

Version:

- **Ground internally and externally.**
- **With Balluff/RFID chip bore.**

All shanks fine bead blasted.

Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835.

Concentricity: $\leq 8 \mu\text{m}$

Overhang dimension A: 95 mm

External \varnothing D: 48 mm

Technical description

Morse taper internal	4
External \varnothing D	48 mm
Overhang dimension A	95 mm
Adapter	SK 50 short
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 8 \mu\text{m}$

Type of product

Arbor adapter