

Garant**Set of parallels, underside magnetic, wide, Length: 125mm****Order data**

Order number	366321 125
GTIN	4062406250508
Item class	31Z

Description**Version:****Accuracy:** Height tolerance ± 0.01 mm; width tolerance ± 0.02 mm.**Hardness:** 48 HRC.**Advantage:**

- Flexible use thanks to integral rod magnet on the underside.
- Reduction in set-up time.

Technical description

Width	10 mm
Height	20 mm
Height	30 mm
Height	35 mm
Height	37 mm
Height	39 mm

Number of strips	5 pair
Type of product	Pairs of parallels

Accessories

Pair of parallels, 125×10Magnetic underside Height 30 mm	366326 30
Pair of parallels, 125×10Magnetic underside Height 39 mm	366326 39
Pair of parallels, 125×10Magnetic underside Height 37 mm	366326 37
Pair of parallels, 125×10Magnetic underside Height 20 mm	366326 20
Pair of parallels, 125×10Magnetic underside Height 35 mm	366326 35