

**HOLEX Pro Drill indexable drill Combination shank, 4xD, Ø DC: 30mm****Order data**

Order number	235010 30
GTIN	4062406253615
Item class	22L

Description**Version:**

HOLEX Pro Drill indexable drills combine cost efficiency with technically fully developed capability.

For use up to 4xD in challenging drilling applications.

Bore tolerance: -0.05 / +0.3 mm

Application:

With indexable inserts No. 235030 – 235082.

Both SOMT inserts for the outer insert seat and also XOMT inserts for the inner insert seat are required.

Supplied with:

With insert screws (supplied without indexable inserts).

Recommendation:

When spot-drilling reduce the feed rate to 70%.

Technical description

Shank Ø D _s	32 mm
Shank length L _s	60 mm

Nominal \varnothing D	30
Reach L_1	123 mm
Pack of insert screws	232980 5 (TX15;3Nm)
ISO code indexable insert	SOMT110408 / XOMT110406
Series	HOLEX Pro
Number of cutting edges Z	1
Overall length L	210 mm
Maximum adjustment limit V_{max}	0.35 mm
Overhang L_A	150 mm
Drill depth for indexable insert drill up to	4xD
Shank	ISO 9766
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Use for drilling	limited oblique spot drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited convexity
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

6 mm blade for Torx® Torx® profile TX15	659922 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500